

Ledonomic complete package

The package contains the following:

- 4 different pictograms: Arrow left, right, down + blank
- Mounting rail for wall
- Jumper for centralization



Ledonomic aluminium or white colors - standard



Order key

| Designation | Type no. color |
|------------------------------------|----------------|
| LEDONOMIC 25M. Complete | E-LN-001 A/W |
| LEDONOMIC 25M. DALI | E-LN-002 A/W |
| FLAG BRACKET | E-LNFF-001 |
| MOUNTING SET, Inner ceiling | E-LNII-001 |
| SABOTAGE/BALL PROTECTION | E-LL015 |
| CEILING PENDLE Aluminium 800 mm | E-LLOO1 |




LEDONOMIC COMPLETE - fits the budget!

Ledonomic is a simpler model of the emergency exit signs with the same high standards and advanced technology as the other products from Ledolight.

Like the previously known Ledosafe, Ledonomic uses LED. This provides high readability and stylish design Ledonomic is developed and manufactured in accordance with the European standard. A long service life, low energy consumption and no maintenance requirements make Ledonomic a cost-effective investment. Manufactured with Swedish quality and design in accordance with the EU and the Swedish laws and norms.

The electrical unit is equipped with sophisticated electronics. Self-testing is a matter of course. Ledonomic is both decentralized and centralized.

- Delivered complete and ready for ceiling and wall installation.



Technical specification

| Material | Aluminium and Acrylic | |
|---|-------------------------------------|--|
| Voltage | 220-240 VAC, 50-60 Hz | |
| Battery | NiMh 4.8 V High Temp 1150 mAh | |
| Backup time | 3 hour | |
| Weight | 950 g | |
| Protection class | IP40 | |
| Energy consumption | 2.7 W | |
| Light source | Light-emitting diodes (LED) 9 items | |
| Reading distance | 25 metres | |
| Self-testing | Yes | |
| Standards EN 60598-1, EN 62471, EN 60598-2-22, EN 1838 | | |
| Decentralized and centralized in the same product - YES | | |





Ledolight Sweden AB Järnvägsgatan 9 SE-441 32 Alingsås, Sweden

Phone: +46 (0)322 19800 E-mail: info@ledolight.se Fax: +46 (0)322 19804

Web: www.ledolight.se